





Technical Details

Designed to Cool:	Orian 1.5T (standard gradient only) Fortian 1.5T		- Hermeti - Variable
Refrigerant:	R454B		- Vertical - E-coatec - Multi-sta
Pump Capacity: Coolant:	100 LPM @ 38 psi Clean, potable dis 35% lab-grade gly	tilled water	- Mult-sta - Closed la - Control a - IP65 sta
Reservoir Volume:	25 gallons	95 liters	- PLC con - Powder-
Electrical: Voltage Tolerance: Min. Circuit Ampacity: Max. Overcurrent Protection:	460V-3Ø-60Hz ±10% 41.8 A 60 A		- Factory - Factory UL rain t
Connections:	1-1⁄2" FNPT		Customi - Remote - Sensors
Shipping Weight:	1,200 lbs	544 kg	
			Certifica

Features

tically sealed scroll compressor

- e speed fan for less noise & improved reliability
- air discharge through microchannel condensers
- ed condensers for corrosion resistance
- tage stainless steel centrifugal pump
- loop design w/ non-ferrous wetted components
- circuit breaker in lieu of fuses
- andard electrical box
- ntroller with alarm descriptions and logging
- r-coated galvanized metal frame and enclosure
- tested under load
- performance testing includes high ambient test, test, and dielectric-voltage test

izations

- e monitoring via cellular connection
- rs to monitor additional critical operating parameters

ations

- cETLus label per UL and CSA specifications
- Seismic certification (OSHPD)

Ambient Air Conditions

-30°F to +120°F -34°C to +49°C Temperature Range: Air Discharge: Vertical Condensers treated for compatibility with coastal installations

Location

- Install outdoors

- proper operation.

Included Accessories

CUSTOMER/PROJECT		CANON MEDICAL SYSTEMS USA, INC.				
DESCRIPTION		OPC15-7BG3C24-MR-12-M538				
† ! ASKRIS	CONFIDENTIAL		CREATED	11 NOV 2020	KSR	
	NOT TO SCALE		UPDATED	17 JAN 2025	KSR	
	SHEET 1	LOF 1	APPROVED	17 JAN 2025	KSR	

- Maintain a clearance of 72" (183cm) on condenser sides - Maintain a clearance of 36" (92cm) on non-condenser side - Maintain an unobstructed space for free air discharge above unit - Consult Haskris if clearances will be smaller than these recommendations. Haskris will evaluate individual site conditions and provide guidance on how to use the smaller space to ensure

- Hand shut off ball valves with flush ports - [3] 5 gallon pails of propylene glycol concentrate